

Table 1: mounting of sensors on cylinders

Series	Ø	CST - CSH	CSV	CSN
24 - 25	16	S-CST-02		
	20	S-CST-03		
	25	S-CST-04		
27	20	S-CST-03		
	25	S-CST-04		
	32	S-CST-18		
	40	S-CST-19		
	50	S-CST-20		
	63	S-CST-21		
31	12	Direct mounting		
	16	Direct mounting		
	20	Direct mounting		
	25	Direct mounting		
	32	Direct mounting		
	40	Direct mounting		
	50	Direct mounting		
	63	Direct mounting		
	80	Direct mounting		
32	100	Direct mounting		
	20	Direct mounting		
	25	Direct mounting		
	32	Direct mounting		
	40	Direct mounting		
	50	Direct mounting		
	63	Direct mounting		
40	80	Direct mounting		
	100	Direct mounting		
	160	S-CST-28		S21
	200	S-CST-28		S21
	250			Direct mounting
41	320			Direct mounting
	160			S53
42	200			S53
	32	S-CST-18		
50	40	S-CST-19		
	50	S-CST-20		
	63	S-CST-21		
	16		Direct mounting	
52	25		Direct mounting	
	32	S-CST-01		
	40	S-CST-01		
	50	S-CST-01		
	63	S-CST-01		
	80	S-CST-01		
	25	Direct mounting		
60	32	Direct mounting		
	40	Direct mounting		
	50	Direct mounting		
	63	Direct mounting		
	80	Direct mounting		
	100	Direct mounting		
60 + 45N	125	S-CST-25		
	32	S-CST-25		
	40	S-CST-25		
	50	S-CST-25		
	63	S-CST-25		
	80	S-CST-26		
	100	S-CST-26		
	125	S-CST-27		
60 + 45N	32	S-CST-45N1		
	40	S-CST-45N1		
	50	S-CST-45N1		
	63	S-CST-45N1		
	80	S-CST-45N2		
100	S-CST-45N2			

Table 2: mounting of sensors on cylinders

Series	Ø	CST - CSH
61	32	Direct mounting
	40	Direct mounting
	50	Direct mounting
	63	Direct mounting
	80	Direct mounting
	100	Direct mounting
	125	Direct mounting
62	32	Direct mounting (CSH only)
	40	Direct mounting (CSH only)
	50	Direct mounting (CSH only)
	63	Direct mounting (CSH only)
	80	Direct mounting (CSH only)
	100	Direct mounting (CSH only)
63...P	32	Direct mounting (CSH only)
	40	Direct mounting (CSH only)
	50	Direct mounting (CSH only)
	63	Direct mounting (CSH only)
	80	Direct mounting (CSH only)
	100	Direct mounting (CSH only)
	125	Direct mounting (CSH only)
63...T	32	S-CST-25
	40	S-CST-25
	50	S-CST-25
	63	S-CST-25
	80	S-CST-26
	100	S-CST-26
	125	S-CST-27
69	32	Direct mounting
	40	Direct mounting
	50	Direct mounting
	63	Direct mounting
	80	Direct mounting
	100	Direct mounting
	125	Direct mounting
6PF	50	Direct mounting
	63	Direct mounting
	80	Direct mounting
	100	Direct mounting
	125	Direct mounting
90	32	S-CST-06
	40	S-CST-07
	50	S-CST-08
	63	S-CST-09
	80	S-CST-10
	100	S-CST-11
	125	S-CST-12
94	16	S-CST-05
	20	S-CST-05
	25	S-CST-05
95	16	S-CST-05
	20	S-CST-05
	25	S-CST-06
97	32	S-CST-06
	40	S-CST-07
	50	S-CST-08
	63	S-CST-09

Table 3: mounting of sensors on cylinders

Series	Ø	CST - CSH	CSV	CSC-D / CSC-H
QC	20	Direct mounting		
	25	Direct mounting		
	32	Direct mounting		
	40	Direct mounting		
	50	Direct mounting		
	63	Direct mounting		
QCBF	20	Direct mounting		
	25	Direct mounting		
	32	Direct mounting		
	40	Direct mounting		
QCTF	20	Direct mounting		
	25	Direct mounting		
	32	Direct mounting		
	40	Direct mounting		
QP - QPR	12		Direct mounting	
	16		Direct mounting	
	20	S-CST-01		
	25	S-CST-01		
	32	S-CST-01		
	40	S-CST-01		
	50	S-CST-01		
	63	S-CST-01		
	80	S-CST-01		
	100	S-CST-01		
	QX	10		
16				Direct mounting
20				Direct mounting
25				Direct mounting
32				Direct mounting
ST		20	Direct mounting	
	32	Direct mounting		
	40	Direct mounting		
	50	Direct mounting		

Table 4: mounting of sensors on grippers, electromechanical axis and cylinders

* Further details about Series 5E electromechanical axis and Series 6E electromechanical cylinders can be found in the C_Electrics catalogue which is also available on the Camozzi website www.camozzi.com within the section Products & Solutions › C_Electrics.

Series	Ø	CST - CSH	CSB-D / CSB-H	CSC-D / CSC-H	CSD-D / CSD-H
Grippers					
CGA	10		Direct mounting		
	16		Direct mounting		
	20		Direct mounting		
	25		Direct mounting		
	32		Direct mounting		
CGC	50		Direct mounting (CSB-D-220 only)		
	64		Direct mounting (CSB-D-220 only)		
	80		Direct mounting (CSB-D-220 only)		
	100		Direct mounting (CSB-D-220 only)		
	125		Direct mounting (CSB-D-220 only)		
CGLN	10			Direct mounting	
	16			Direct mounting	
	20			Direct mounting	
	25			Direct mounting	
	32			Direct mounting	
CGP	10		Direct mounting		
	16		Direct mounting		
	20		Direct mounting		
	25		Direct mounting		
	32		Direct mounting		
CGPS	10				Direct mounting
	16				Direct mounting
	20				Direct mounting
	25				Direct mounting
	32				Direct mounting
CGPT	16				Direct mounting
	20				Direct mounting
	25				Direct mounting
	32				Direct mounting
	40				Direct mounting
CGSN	16			Direct mounting	Direct mounting
	20			Direct mounting	Direct mounting
	25			Direct mounting	Direct mounting
	32			Direct mounting	Direct mounting
RPGB	8				Direct mounting
	12				Direct mounting
Electromechanical axis *					
5E	50	Direct mounting (CSH only)			
	65	Direct mounting (CSH only)			
	80	Direct mounting (CSH only)			
Electromechanical cylinders *					
6E	32	Direct mounting			
	40	Direct mounting			
	50	Direct mounting			
	63	Direct mounting			